

Designation	Description	Notes	Art. No.
Evaporator cover	An evaporator cover can be installed for added safety, to ensure that cold-sensitive products cannot touch the evaporator.		EVPL100
Shelves plastic-coated	Additional plastic-coated grid shelves can be retrofitted as required to provide extra storage options. The sturdy grid shelves have an extremely high loading capacity of up to 45 kg.		SHL100
Glass shelves	Additional glass shelves can be retrofitted to the LC-LG-LX Series as required to provide extra storage options. The glass shelves made of toughened safety glass meet the standards for spark-free refrigerators in accordance with ATEX 95 and have a loading capacity of up to 40 kg.		GHL100
Baskets	The optional baskets provide an optimum overview of the stored preparations and can help to improve the handling and organising of the freezer contents.		BHL100
Drawers	The drawers reduce loss of cold air during door opening and can be used to store small items or opened packages		DHL100
Adjustable legs	Adjustable-height feet can be retrofitted for easy cleaning underneath. They are adjustable between 115 mm and 170 mm in height.		LEG100
Castor base	A castor base is available as an accessory to allow flexible use of the appliances in different rooms.		CAS100
Additional lock barrels	Up to 10 additional lock barrels to protect the stored products against unauthorised access are available as accessories for the laboratory appliances. In case of multiple appliances, different locks can be installed to ensure that the respective appliance can only be accessed by the staff members responsible for it.		ALK100

Notes